

GHIBLI-II DRY CABINETS

Moisture Sensitive Devices (MSDs), must be managed correctly because "a single mistake" on a tray or reel of MSD causes "negative impact on the entire production batch".

Electronic components (like QFP, BGA or SOIC for example), LEDs and Printed Circuit Boards, when extracted from their original protective package, absorb humidity from the environment and during the soldering process the trapped moisture can vaporize and exert internal package stress.

GHIBLI-II dry cabinets provides a "safe place" to temporary stock the MSDs removed from their original Dry Pack before soldering process.

In fact the J-STD-033 tells that under 5% RH the Floor Life is congealed.



8104.812



8104.808

Technical specifications

Humidity range:	<5% RH guaranteed , typical 2% RH
Colour:	Anthracite
Power supply:	230Vac
Structure:	1 mm thick carbon steel with antistatic paint
Door:	magnetic handles , magnetic sealers and antistatic glass
Wheel:	4 antistatic 3" wheels, two of them with brakes
Grounding wire:	940mm long
ESD paint:	$10^3 - 10^9 \Omega$



DryLogger (included in every cabinet)

Humidity: 1 to 95% RH
 resolution: 0.1%RH
 Temperature: -20°C to +60°C,
 resolution: 0.1°C
 ALARM for Max.humidity and Max temperature

(see page 77)

Advantages about GHIBLI-II

Easy use:

It's plug and play, just connect it to the main supply without any settings and it will be stable at less than 5%RH (5%RH is guaranteed but the cabinets easily reach 2%).

The dehumidifier units are always active and not controlled by any sensor. This avoid dangerous problems due to malfunction or drift of hygrometers.

Easy calibration:

Inside every cabinet there is a portable Hygrometer (DryLogger 9265.300) visible through the glass of the upper door. You can return it for calibration anytime without problems: the cabinet still works to the best.


The portable instrument DryLogger can measure RH & Temperature values in several points inside the cabinet, and can record H/T and transfer the data to PC for graphing and analyzing. Made for very low humidity measurement can be used also for applications outside the cabinets.

Modular design:

The dehumidifier modules are easy extractable with only a screwdriver. This allow easy reparation and grant the long life of the cabinet, over 20 years, as long as the metal structure last. This is our green policy.

Smart magnetic handles with key lock at every door. The front of the cabinet is flat.

2 years warranty



Data analysis








With the portable instrument DryLogger and the software LogManager supplied with every cabinet you can calculate the time intervals and percentage that exceed the 10%RH or 5%RH which leads to the estimation of the MSD floor life ("Floor Life" is the allowable time period after removal from a moisture barrier bag, dry storage or dry bake and before the solder process reflow).

Another typical data analysis is the graph of the door opening.

40°C Baking

Some cabinets version can do 40°C low baking process of SMD components.

At this temperature the reels are not damaged and can be afterwards inserted into the feeders of the pick and place without problems.

							
Code	8104.800	8104.802	8104.804	8104.808	8104.812	8104.830	8104.832
Model	Ghibli II/200L	Ghibli II/328L	Ghibli II/400L	Ghibli II/600L	Ghibli II/1200L	Ghibli II/600L 40°C baking	Ghibli II/1200L 40°C baking
Capacity	200L	328L	400L	650L	1280L	600L	1180L
Ext. Dimensions (mm)	600x672x610	905x452x1045	600x672x1255	600x672x1805	1200x672x1805	600x672x1805	1200x672x1805
Shelves	2	3	3	5	5	5	5
Shelf Size (mm)	555x530x20	860x310x20	555x530x20	555x530x20	1155x530x20	555x530x20	1155x530x20
Average power	28W	56W	56W	56W	56W	56W without baking 456W with baking	56W without baking 856W with baking
Maximum power	210W	420W	420W	420W	420W	420W without baking 1220W with baking	420W without baking 2020W with baking
Weight	55kg	64kg	64kg	81kg	134kg	91kg	144kg

8104.840 Additional shelf 555x530x20mm , Ghibli-II 200L, 400L, 600L

8104.841 Additional shelf 1155x530x20mm , Ghibli-II 1200L

ALARM BOX

With this option it's possible to set an alarm that become active when, after a certain period of time, humidity or temperature are above a predetermined maximum threshold.

The Alarm Box has a warning light and a buzzer that can be silenced from a switch on the panel.



8104.856

Alarm Box for Ghibli-II cabinets

TRAY RACK

Professional tray rack made of stainless steel that can be placed on the trays of the Ghibli-II dry cabinets.



8104.865
8104.583

GHIBLI-II - RACK 10 trays store
Aluminium tray 530 x 500 x 12mm